## Type LPC-02 In-Line Fuse Holder 5 x 20mm Fuses




www.optifuse.com (619) 593-5050

Part number format

## **Ratings:**

Fuse Type: 5 x 20mmLPC-02B-##RElectrical Rating: 10A 500VAC, 10A 32VDCwhere ## = Wire gaugeBody: Nylon (UL94V-0)where ## = Wire gaugeContacts: BrassStandard Wire Sizes: #16 AWG (UL1015)Standard Wire Colors: RedStandard Body colors: BlackStandard Wire Length: 13 inches (331mm)Available in various wire gauges and lengths, and body and wire colors.Contact factory for those not listed above.

## Mechanical Dimensions: Inches [mm]





-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.