Type BLR-I-506 Fuse Block - Indicating 6 Pole - Regular Auto Blade



www.optifuse.com

(619) 593-5050

Specifications:

Voltage: 32 VDC

Max Current Rating: 30A per Circuit - 100A Max Input


Fuse Type: Regular Auto Blade – APR / ANR

Base: PBT (UL flame: 94V-0), Black **Cover:** PC (UL flame: 94V-2), Transparent

Push Button: POM (White) **Terminals:** Copper, Tin plated **Indicating LED** – Red

Temperature Rating: -20° C ~ +85° C

Mechanical Dimensions: Inches [mm]



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.

Note: All specifications subject to change without notice.

Rev B 04/2017 - Page: 1/1 Code S02-01H