


# ATO® ADD-A-CIRCUIT® SERIES

## 32V IN-LINE FUSE HOLDER



0FHA0200Z

### Specifications

<b>Current Rating Continuous:</b>	7.5A
<b>Current Rating Max:</b>	10A
<b>Fuse Type:</b>	ATO® Fuses
<b>Mounting Method:</b>	In-Line Fuse Holder Blades / Butt Splice Connector
<b>Max Voltage Rating:</b>	32VDC

### Description

The ATO® Add-A-Circuit® Series 32V In-Line Fuse Holder allows easy installation of an added circuit without cutting or splicing. The ATO® fuse tap turns a single fuse slot into two so you can protect the new accessory circuit as well as the existing circuit.

This fuse tap features 16 AWG UL 1015 wire leads and butt splice connectors to make in-line installation simple.

The ATO® Add-A-Circuit® Series fuse tap is available in bulk or as a carded blister packaged ATO® Add-A-Circuit® Series kit that comes with a set of ATO® blade fuses. The fuse set includes one 3-amp, one 5-amp, one 7.5-amp, and one 10-amp fuse.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/ATO-AddACircuit](http://littelfuse.com/ATO-AddACircuit)

### Applications

- Accessory Circuits

### Features and Benefits

- Compatible with ATO® blade fuses rated up to 10 amps
- Turns one fuse slot into two to protect an added accessory circuit without cutting or splicing
- Butt splice connectors ensure easy wiring
- Red 16 AWG UL 1015 wire leads
- Available ATO® Add-A-Circuit® Series blister packaged fuse tap kit comes with a set of fuses (3A, 5A, 7.5A, and 10A)

### Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
0FHA0200Z	32V In-Line Fuse Holder	ATO Fuse	In-Line Fuse Holder Blades / Butt Splice Connector	10 AMPS	32 VDC
0FHA0200ZP	32V In-Line Fuse Holder Kit with Fuses - Blister Pack	ATO Fuse	In-Line Fuse Holder Blades / Butt Splice Connector	10 AMPS	32 VDC