Type LPA-02 **In-Line Fuse Holder - Heavy Duty** ¹/₄" x 1¹/₄" (6.3 x 32mm) Fuses



www.optifuse.com

(619) 593-5050

Ratings:

Fuse Type: ¹/₄" x 1¹/₄" (6.3 x32mm) Electrical Rating: 250VAC, 32VAC **Body:** Nylon with glass fiber **Contacts:** Brass Standard Wire Sizes: #12 ~ #18 AWG Standard Wire Colors: Red Standard Body colors: White Standard Wire Length: 4 inches


Part number format LPA-02W-##R

where ## = Wire gauge

Wire Gauge	Max. Amperage
12 AWG	30 A
14 AWG	20 A
16 AWG	15 A
18 AWG	10 A

Available in various wire gauges and lengths, and body and wire colors. Contact factory for those not listed above.

Mechanical Dimensions: Inches [mm]



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance. -Not designed for prolonged liquid exposure or submersible applications.

Rev D 11/2021 - Page: 1/1 Code J01-02D