Type LPM-05 Water-Proof In-Line Fuse Holder Automotive Mini. Blade Type



www.optifuse.com

(619) 593-5050

Specifications:

Rating: 32VDC

Body/Cap Material: Polycarbonate **Seal Material:** Silicon rubber **Canta et al.** Propuse. Tie (Nieleal plate de la late de late de la late de lat

Contacts: Bronze, Tin/Nickel plated

IP Rating: IP67

For use w/ Type APM, ANR Fuse (Miniature Automotive Blade)

Water-proof with Inter-Locking Cap

Attached Mounting Bracket

Standard Wire: #12, #14, #16 AWG – 12" Loop - Red Color (Other wire sizes and colors available as special order)

Part number format


LPM-05B-##R

Where

= Wire Gauge (12,14,16 AWG)

Wire Gauge	Max. Amperage
12 AWG	30 A
14 AWG	20 A
16 AWG	15 A

Mechanical Dimensions: Inches [mm]





-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



- -Device are intended for occasional overcurrent protection. Application for repeated overcurrent condition and/or prolonged trip are not anticipated.
- -Avoid contact of device with chemical solvent. Prolonged contact will damage the device performance.
- Not intended for submersible water applications.

Note: All specifications subject to change without notice.

Rev A 07/2018 - Page: 1/1 Code B01-01H