

Type BLS-I-310

Fuse Block - Indicating

10 Pole-Low Profile Mini Auto Blade




www.optifuse.com

(619) 593-5050

Specifications:

- Max Current Rating:** 30A per Circuit - 100A Max Input
- Fuse Type:** Low Profile Miniature Auto Blade – APS, ANS series
- Base:** PBT (UL-Flame 94V-0), Black
- Cover:** PC (UL-Flame 94V-2), Transparent
- Terminals:** Tin Plated Brass - 0.250" Quick Connect Terminals
- Indicating LED** – Red
- Temperature Rating:** -20° C ~ +85° C

Mechanical Dimensions: Inches [mm]



Warning:



- Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.
- Avoid contact of device with chemical solvent. Prolonged contact may damage the device performance.