Type PMA-DS-07-SOS Panel Mount Fuse Holder 1/4" x 11/4" (6.3 x 32mm) Fuses Driver / Screw



www.optifuse.com

(619) 593-5050

Electrical Rating: 20A, 250V AC **Fuse Style:** 1/4" x 11/4" (6.3 x 33mm)


Material:

Frame and Cap: Nylon (UL flame: 94V-2)

Terminals: Nickel-plated brass Cap: Slotted Driver type, Screw type Mounting: by nut and washer Terminal: Solder 6.4mm / 0.25" Panel Thickness: 0.5 ~ 7mm Agency Standards and Listings:

c **FL** us

Product Dimensions: Inches [mm]



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Fuse Holders are not intended for circuit disconnect. All power should be disconnected before removing fuse.

-Avoid contact of Fuse Holder with chemical solvent. Prolonged contact may damage the device performance.