



Wire-end ferrules, Max. wire cross-section: 120 mm<sup>2</sup>, Length: 32 mm, Colour: natural

### Business data

Article number	2792.0
Article name	H 120,0/32
GTIN (EAN)	4044211055219
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	8.05 g
Weight per piece (including packaging)	8.12 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

---

### Technical data

---

#### Dimensions

Length	32 mm
Diameter of copper pipe	17.2 mm
Diameter of feed-in funnel	19 mm
Wall thickness of copper pipe	0.5 mm

#### Connection data

Wire cross-section, max.	120 mm <sup>2</sup>
Wire cross-section AWG, max.	4/0
Stripping length	32 mm

#### Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

## 2792.0 H 120,0/32



---

### Approvals

---

#### Standards and regulations

---

DIN 46228-1:1992	yes
------------------	-----

---

# Data sheet

## 2792.0 H 120,0/32



---

### Media

---

---

### Accessories

---