



Wire-end ferrules, Max. wire cross-section: 1 mm<sup>2</sup>, Length: 18 mm, Length of copper pipe: 12 mm, Colour: Red

### Business data

Article number	2840.0
Article name	H 1,0/18-D RD
GTIN (EAN)	4044211055653
Packaging unit	500
Quantity unit	PC
Weight per piece (not including packaging)	0.11 g
Weight per piece (including packaging)	0.12 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Red

### Technical data

#### Dimensions

Length	18 mm
Length of copper pipe	12 mm
Diameter of copper pipe	1.4 mm
Diameter plastic collar	3 mm
Wall thickness of copper pipe	0.15 mm
Wall thickness of plastic collar	0.25 mm

#### Connection data

Wire cross-section, max.	1 mm <sup>2</sup>
Wire cross-section AWG, max.	17
Stripping length	14 mm

#### Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

#### Further technical data

Insulation available	✓
----------------------	---

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

2840.0 H 1,0/18-D RD



---

## Approvals

---

### Standards and regulations

---

DIN 46228-4:1990

yes

---

# Data sheet

2840.0 H 1,0/18-D RD



---

Media

---

---

### Accessories

---