



Wire-end ferrules, Max. wire cross-section: 2.5 mm², Length: 7 mm, Colour: natural

Business data

Article number	2223.0
Article name	H 2,5/7
GTIN (EAN)	4044211050467
Packaging unit	1000
Quantity unit	PC
Weight per piece (not including packaging)	0.08 g
Weight per piece (including packaging)	0.09 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

Technical data

Dimensions

Length	7 mm
Diameter of copper pipe	2.2 mm
Diameter of feed-in funnel	3.4 mm
Wall thickness of copper pipe	0.15 mm

Connection data

Wire cross-section, max.	2.5 mm ²
Wire cross-section AWG, max.	14
Stripping length	7 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2223.0 H 2,5/7



Approvals

Standards and regulations

DIN 46228-1:1992

yes

Media

Accessories
