

3092.0 H 1,0/8-D AWG RD

Wire-end ferrules, Max. wire cross-section: 1 mm², Length: 14 mm, Length of copper pipe: 8 mm, Colour: Red

Business data

Article number	<u>3092.0</u>
Article name	H 1,0/8-D AWG RD
GTIN (EAN)	4044211057978
Packaging unit	500
Quantity unit	PC
Weight per piece (not including packaging)	0.11 g
Weight per piece (including packaging)	0.12 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Red

Technical data

Dimensions

Length	14 mm
Length of copper pipe	8 mm
Diameter of copper pipe	1.4 mm
Diameter plastic collar	3.5 mm
Wall thickness of copper pipe	0.15 mm
Wall thickness of plastic collar	0.25 mm

Connection data

Wire cross-section, max.	1 mm ²
Wire cross-section AWG, max.	17
Stripping length	10 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

Standards and regulations

DIN 46228-4:1990	yes
------------------	-----

Media

Accessories
