

Data sheet

2793.0 H 150,0/32



Wire-end ferrules, Max. wire cross-section: 150 mm², Length: 32 mm, Colour: natural

Business data

Article number	2793.0
Article name	H 150,0/32
GTIN (EAN)	4044211055226
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	10.27 g
Weight per piece (including packaging)	10.4 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

Technical data

Dimensions

Length	32 mm
Diameter of copper pipe	19.5 mm
Diameter of feed-in funnel	21 mm
Wall thickness of copper pipe	0.5 mm

Connection data

Wire cross-section, max.	150 mm ²
Wire cross-section AWG, max.	250 kcmil
Stripping length	32 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2793.0 H 150,0/32



Approvals

Standards and regulations

DIN 46228-1:1992	yes
------------------	-----

Data sheet

2793.0 H 150,0/32



Media

Accessories
