

## 2882.0 H 1,5/14 D-B Rolle BK (5.000 St.)



Wire-end ferrules, Max. wire cross-section: 1.5 on roll mm<sup>2</sup>, Length: 14 mm, Length of copper pipe: 8 mm, Colour: Black

**RAL:** 9005

### Business data

|  |                                   |
|--|-----------------------------------|
| Article number                             | 2882.0                            |
| Article name                               | H 1,5/14 D-B Rolle BK (5.000 St.) |
| GTIN (EAN)                                 | 4044211056070                     |
| Packaging unit                             | 1                                 |
| Quantity unit                              | PC                                |
| Weight per piece (not including packaging) | 0.18 g                            |
| Weight per piece (including packaging)     | 0.2 g                             |
| Unit of weight                             | G                                 |
| Customs number                             | 85369010                          |
| Country of origin                          | DE                                |
| Product description                        | Wire-end ferrules on roll         |
| Colour                                     | Black                             |

## 2882.0 H 1,5/14 D-B Rolle BK (5.000 St.)

### Technical data

#### Dimensions

|                                  |         |
|----------------------------------|---------|
| Length                           | 14 mm   |
| Length of copper pipe            | 8 mm    |
| Diameter of copper pipe          | 1.7 mm  |
| Diameter plastic collar          | 3.5 mm  |
| Wall thickness of copper pipe    | 0.15 mm |
| Wall thickness of plastic collar | 0.25 mm |

#### Connection data

|                              |                     |
|------------------------------|---------------------|
| Wire cross-section, max.     | 1.5 mm <sup>2</sup> |
| Wire cross-section AWG, max. | 16                  |
| Stripping length             | 10 mm               |

#### Materials

|                           |                                |
|---------------------------|--------------------------------|
| Copper pipe               | Copper alloy                   |
| Surface                   | Galvanically tin-plated, shiny |
| Plastic collar            | Polypropylene homopolymer      |
| Working temperature, min. | -5 °C                          |
| Working temperature, max. | 105 °C                         |

#### Further technical data

|                      |   |
|----------------------|---|
| Insulation available | ✓ |
|----------------------|---|

#### Environmental Product Compliance

|                                |            |
|--------------------------------|------------|
| REACH Conform                  | yes        |
| REACH Reference date           | 2023-06-14 |
| REACH Candidate Substance Note | No         |
| RoHS Conform                   | yes        |

## 2882.0 H 1,5/14 D-B Rolle BK (5.000 St.)

---

### Approvals

---

### Standards and regulations

---

DIN 46228-4:1990

yes

---

### Media

---

## 2882.0 H 1,5/14 D-B Rolle BK (5.000 St.)

### Accessories

#### ##INVERSE##CONTA-CONNECT



Screw-distributor block, Screw connection, Mounting type:Mounting rail TS 35/7.5 and mounting surface, Rated cross-section of input: 70 mm<sup>2</sup>, Rated cross-section of output: 16 mm<sup>2</sup>, Colour: Light grey

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>1746.0</u>  | SVB 160 LG   | 4044211143534 | 1 ST           |



Screw-distributor block, Screw connection, Mounting type:Mounting rail TS 35/7.5 and mounting surface, Rated cross-section of input: 70 mm<sup>2</sup>, Rated cross-section of output: 16 mm<sup>2</sup>, Colour: Light grey

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>1745.0</u>  | SVB 175/3 LG | 4044211143527 | 1 ST           |