



Crimp lug, Fork shape acc. to DIN 46237/C, Max. wire cross-section: 6 mm², Colour: Yellow

RAL: 1026

Business data

Article number	<u>3070.0</u>
Article name	QKS G 6
GTIN (EAN)	4044211057756
Connector shape	Fork shape acc. to DIN 46237/C
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	1.6 g
Weight per piece (including packaging)	1.62 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Yellow

Technical data

Dimensions

Length (input to end of inner fork ring)	21 mm
Outer width of fork	8 mm
Inner width of fork	4.3 mm
Diameter of feed-in funnel	21 mm
Size DIN	C 4 - 6

Connection data

Wire cross-section, min.	4 mm ²
Wire cross-section, max.	6 mm ²
Wire cross-section AWG, min.	12
Wire cross-section AWG, max.	10

Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
Soldered	✓

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

3070.0 QKS G 6



Approvals

Standards and regulations

Standards / specifications

DIN EN 13599

Data sheet

3070.0 QKS G 6



Media

Accessories
