



Wire-end ferrules, Max. wire cross-section: 6 mm², Length: 18 mm, Colour: natural

Business data

Article number	3105.0
Article name	H 6,0/18
GTIN (EAN)	4044211058104
Packaging unit	500
Quantity unit	PC
Weight per piece (not including packaging)	0.36 g
Weight per piece (including packaging)	0.37 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

Technical data

Dimensions

Length	18 mm
Diameter of copper pipe	3.5 mm
Diameter of feed-in funnel	4.7 mm
Wall thickness of copper pipe	0.2 mm

Connection data

Wire cross-section, max.	6 mm ²
Wire cross-section AWG, max.	10
Stripping length	18 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

3105.0 H 6,0/18



Approvals

Standards and regulations

DIN 46228-1:1992	yes
------------------	-----

Data sheet

3105.0 H 6,0/18



Media

Accessories
