



Crimp lug, Ring shape acc. to DIN 46237, Max. wire cross-section: 6 mm<sup>2</sup>, Colour: Yellow

**RAL:** 1026

### Business data

Article number	<u>2543.0</u>
Article name	QKS 6
GTIN (EAN)	4044211053369
Connector shape	Ring shape acc. to DIN 46237
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	1.97 g
Weight per piece (including packaging)	2.02 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Yellow

### Technical data

#### Dimensions

Length (input to middle of the ring hole)	23 mm
Width of ring	11 mm
Ring hole diameter	6.5 mm
Diameter of feed-in funnel	6.5 mm
Size DIN	A 6 - 6

#### Connection data

Wire cross-section, min.	4 mm <sup>2</sup>
Wire cross-section, max.	6 mm <sup>2</sup>
Wire cross-section AWG, min.	12
Wire cross-section AWG, max.	10

#### Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

#### Further technical data

Insulation available	✓
Soldered	✓

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

## 2543.0 QKS 6



---

### Approvals

---

#### Standards and regulations

---

Standards / specifications

DIN EN 13599

---

---

**Media**

---

---

**Accessories**

---