

Data sheet

2791.0 H 95,0/32



Wire-end ferrules, Max. wire cross-section: 95 mm², Length: 32 mm, Colour: natural

Business data

Article number	2791.0
Article name	H 95,0/32
GTIN (EAN)	4044211055202
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	5.74 g
Weight per piece (including packaging)	5.78 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

Technical data

Dimensions

Length	32 mm
Diameter of copper pipe	14.5 mm
Diameter of feed-in funnel	17 mm
Wall thickness of copper pipe	0.3 mm

Connection data

Wire cross-section, max.	95 mm ²
Wire cross-section AWG, max.	3/0
Stripping length	32 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2791.0 H 95,0/32



Approvals

Standards and regulations

DIN 46228-1:1992

yes

Data sheet

2791.0 H 95,0/32



Media

Accessories
