

## 2889.0 H 0,34/14 D-B Rolle CY (5.000 St.)



Wire-end ferrules, Max. wire cross-section: 0.34 on roll mm<sup>2</sup>, Length: 14 mm, Colour: Cyan

### Business data

Article number	2889.0
Article name	H 0,34/14 D-B Rolle CY (5.000 St.)
GTIN (EAN)	4044211056148
Packaging unit	1
Quantity unit	PC
Weight per piece (not including packaging)	0.07 g
Weight per piece (including packaging)	0.9 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Wire-end ferrules on roll
Colour	Cyan

## 2889.0 H 0,34/14 D-B Rolle CY (5.000 St.)

### Technical data

#### Dimensions

Length	14 mm
Diameter of copper pipe	0.85 mm
Diameter plastic collar	2 mm
Wall thickness of copper pipe	0.15 mm
Wall thickness of plastic collar	0.25 mm

#### Connection data

Wire cross-section, max.	0.34 mm <sup>2</sup>
Wire cross-section AWG, max.	22

#### Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

#### Further technical data

Insulation available	✓
----------------------	---

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet



**2889.0 H 0,34/14 D-B Rolle CY (5.000 St.)**

---

## Approvals

---

### Standards and regulations

---

DIN 46228-4:1990

yes

---

# Data sheet



2889.0 H 0,34/14 D-B Rolle CY (5.000 St.)

---

Media

---

### Accessories

---