

# Data sheet

## 3102.0 H 4,0/15



Wire-end ferrules, Max. wire cross-section: 4 mm<sup>2</sup>, Length: 15 mm, Colour: natural

### Business data

Article number	3102.0
Article name	H 4,0/15
GTIN (EAN)	4044211058074
Packaging unit	1000
Quantity unit	PC
Weight per piece (not including packaging)	0.15 g
Weight per piece (including packaging)	0.16 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

---

### Technical data

---

#### Dimensions

Length	15 mm
Diameter of copper pipe	2.8 mm
Diameter of feed-in funnel	4 mm
Wall thickness of copper pipe	0.2 mm

#### Connection data

Wire cross-section, max.	4 mm <sup>2</sup>
Wire cross-section AWG, max.	12
Stripping length	15 mm

#### Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

## 3102.0 H 4,0/15



---

### Approvals

---

### Standards and regulations

---

DIN 46228-1:1992	yes
------------------	-----

---

# Data sheet

## 3102.0 H 4,0/15



---

### Media

---

---

**Accessories**

---