

# Data sheet

## 2220.0 H 1,0/10



Wire-end ferrules, Max. wire cross-section: 1 mm<sup>2</sup>, Length: 10 mm, Colour: natural

### Business data

Article number	2220.0
Article name	H 1,0/10
GTIN (EAN)	4044211050436
Packaging unit	1000
Quantity unit	PC
Weight per piece (not including packaging)	0.07 g
Weight per piece (including packaging)	0.08 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

---

### Technical data

---

#### Dimensions

Length	10 mm
Diameter of copper pipe	1.4 mm
Diameter of feed-in funnel	2.5 mm
Wall thickness of copper pipe	0.15 mm

#### Connection data

Wire cross-section, max.	1 mm <sup>2</sup>
Wire cross-section AWG, max.	17
Stripping length	10 mm

#### Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

## 2220.0 H 1,0/10



---

### Approvals

---

#### Standards and regulations

---

DIN 46228-1:1992

yes

---

# Data sheet

## 2220.0 H 1,0/10



---

### Media

---

---

**Accessories**

---