



Crimp lug, Pin shape acc. to DIN 46231, Length: 23.5 mm, Max. wire cross-section: 1 mm², Colour: Red

Business data

Article number	2545.0
Article name	SKS 1
GTIN (EAN)	4044211053383
Connector shape	Pen shape acc. to DIN 46231
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.7 g
Weight per piece (including packaging)	0.71 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Red

Technical data

Dimensions

Length	23.5 mm
Length of pin	10.5 mm
Width of pin	1.9 mm
Diameter of feed-in funnel	4.1 mm
Size DIN	1

Connection data

Wire cross-section, min.	0.5 mm ²
Wire cross-section, max.	1 mm ²
Wire cross-section AWG, min.	20
Wire cross-section AWG, max.	18

Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
Soldered	✓

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2545.0 SKS 1



Approvals

Standards and regulations

Standards / specifications

DIN EN 13599

Media

Accessories
