



Wire-end ferrules, Max. wire cross-section: 4 mm², Length: 22 mm, Length of copper pipe: 12 mm, Colour: Orange

Business data

Article number	<u>3041.0</u>
Article name	HZL 4,0-T OG
GTIN (EAN)	4044211057466
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.47 g
Weight per piece (including packaging)	0.48 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Orange

Data sheet

3041.0 HZL 4,0-T OG

Technical data

Dimensions

Length	22 mm
Length of copper pipe	12 mm
Width of plastic collar	5.2 mm
Height of plastic collar	9 mm
Diameter of copper pipe	3.5 mm
Wall thickness of copper pipe	0.2 mm
Wall thickness of plastic collar	0.5 mm

Connection data

Wire cross-section, max.	4 mm ²
Wire cross-section AWG, max.	12
Stripping length	15 mm
2-wire plastic collar	✓

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

Standards and regulations

DIN 46228-4:1990

yes

Media

Accessories
