

Data sheet

2229.0 H 10,0/18



Wire-end ferrules, Max. wire cross-section: 10 mm², Length: 18 mm, Colour: natural

Business data

| | |
|--|---------------|
| Article number | 2229.0 |
| Article name | H 10,0/18 |
| GTIN (EAN) | 4044211050528 |
| Packaging unit | 500 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 0.49 g |
| Weight per piece (including packaging) | 0.5 g |
| Unit of weight | G |
| Customs number | 85369010 |
| Country of origin | DE |
| Product description | Ferrules |
| Colour | Natural |

Technical data

Dimensions

| | |
|-------------------------------|--------|
| Length | 18 mm |
| Diameter of copper pipe | 4.5 mm |
| Diameter of feed-in funnel | 5.8 mm |
| Wall thickness of copper pipe | 0.2 mm |

Connection data

| | |
|------------------------------|--------------------|
| Wire cross-section, max. | 10 mm ² |
| Wire cross-section AWG, max. | 8 |
| Stripping length | 18 mm |

Materials

| | |
|---------------------------|--------------------------------|
| Copper pipe | Copper alloy |
| Surface | Galvanically tin-plated, shiny |
| Working temperature, max. | 120 °C |

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

Data sheet

2229.0 H 10,0/18



Approvals

Standards and regulations

| | |
|------------------|-----|
| DIN 46228-1:1992 | yes |
|------------------|-----|

Data sheet

2229.0 H 10,0/18



Media

Accessories
