Mc	aterial			High Conductivity Seamless Copper Tube				
Plo	iting			Electro-Tin				
Wire Size			750 kcmil	.63±.07 .705 R REF				
Wire Type				Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric		PANDUIT c <sup>(l)</sup> us 750 kcmil		
Wire Strip Length		l	2-15/16 in.	3.00±.08 1.75±.02				
Stud Size				1/2 in.				
	Listed Wire onnector		Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.07	1.75±.	.56±.02 DIA		
	Temperature ating S.A. Certified ire Connector			90° C N/A		1.701	(4) PLS	
							7.25±.09►	
Panduit Color Code on Barrel		ode	BLACK					
	Panduit Die Index No. on Barrel		x No.	P106			2.88±.09 Bevele	
Die	Alternate Industry Die Index No. ( ) on Barrel			(24)			entry	
						.26±.02		
							CORP. TINLEY PARK, ILLINO	
)1	9/17	JHNU	JHNU	REVISED DIMENSIONS, TOLERANCES	5	014695	LCP750-12-3	
00	11/16	/16 JHNU JHNU DRAWING RELEASED			Copper Lug - Four Hole, Long Barrel			
							SCALE DRAWING NO / CAD FILE	