



Wire-end ferrules, Max. wire cross-section: 95 mm², Length: 44 mm, Length of copper pipe: 25 mm, Colour: Red

Business data

Article number	<u>2787.0</u>
Article name	H 95,0/44 RD
GTIN (EAN)	4044211055165
Packaging unit	25
Quantity unit	PC
Weight per piece (not including packaging)	5 g
Weight per piece (including packaging)	5.2 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Red

Technical data

Dimensions

Length	44 mm
Length of copper pipe	25 mm
Diameter of copper pipe	14.7 mm
Diameter plastic collar	18 mm
Wall thickness of copper pipe	0.35 mm
Wall thickness of plastic collar	0.6 mm

Connection data

Wire cross-section, max.	95 mm ²
Wire cross-section AWG, max.	3/0
Stripping length	31 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2787.0 H 95,0/44 RD



Approvals

Standards and regulations

DIN 46228-4:1990

yes

Data sheet

2787.0 H 95,0/44 RD



Media

Accessories
