



Wire-end ferrules, Max. wire cross-section: 35 mm<sup>2</sup>, Length: 39 mm, Length of copper pipe: 25 mm, Colour: Red

### Business data

Article number	2860.0
Article name	H 35,0/39-D RD
GTIN (EAN)	4044211055851
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	2.5 g
Weight per piece (including packaging)	2.51 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Red

### Technical data

#### Dimensions

Length	39 mm
Length of copper pipe	25 mm
Diameter of copper pipe	8.3 mm
Diameter plastic collar	12.7 mm
Wall thickness of copper pipe	0.2 mm
Wall thickness of plastic collar	0.4 mm

#### Connection data

Wire cross-section, max.	35 mm <sup>2</sup>
Wire cross-section AWG, max.	2
Stripping length	28 mm

#### Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

#### Further technical data

Insulation available	✓
----------------------	---

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

2860.0 H 35,0/39-D RD



---

## Approvals

---

### Standards and regulations

---

DIN 46228-4:1990	yes
------------------	-----

---

---

### Media

---

---

### Accessories

---