



Wire-end ferrules, Max. wire cross-section: 2.5 mm², Length: 19 mm, Length of copper pipe: 10 mm, Colour: Grey

RAL: 7032

Business data

| | |
|--|---------------|
| Article number | 3038.0 |
| Article name | HZL 2,5-T GR |
| GTIN (EAN) | 4044211057435 |
| Packaging unit | 500 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 0.32 g |
| Weight per piece (including packaging) | 0.34 g |
| Unit of weight | G |
| Customs number | 85369010 |
| Country of origin | DE |
| Product description | Ferrules |
| Colour | Grey |

Data sheet

3038.0 HZL 2,5-T GR

Technical data

Dimensions

| | |
|----------------------------------|---------|
| Length | 19 mm |
| Length of copper pipe | 10 mm |
| Width of plastic collar | 4.5 mm |
| Height of plastic collar | 8 mm |
| Diameter of copper pipe | 2.8 mm |
| Wall thickness of copper pipe | 0.15 mm |
| Wall thickness of plastic collar | 0.4 mm |

Connection data

| | |
|------------------------------|---------------------|
| Wire cross-section, max. | 2.5 mm ² |
| Wire cross-section AWG, max. | 14 |
| Stripping length | 13 mm |
| 2-wire plastic collar | ✓ |

Materials

| | |
|---------------------------|--------------------------------|
| Copper pipe | Copper alloy |
| Surface | Galvanically tin-plated, shiny |
| Plastic collar | Polypropylene homopolymer |
| Working temperature, min. | -5 °C |
| Working temperature, max. | 105 °C |

Further technical data

| | |
|----------------------|---|
| Insulation available | ✓ |
|----------------------|---|

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

Approvals

Standards and regulations

DIN 46228-4:1990

yes

Media

Accessories
