



Crimp lug, Length: 21.3 mm, Max. wire cross-section: 2.5 mm², Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	<u>2559.0</u>
Article name	FST 2,5/6,3
GTIN (EAN)	4044211053529
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.96 g
Weight per piece (including packaging)	1 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Blue

Technical data

Dimensions

Length	21.3 mm
Length of connector	8 mm
Plug width	6.3 mm
Diameter of feed-in funnel	4.3 mm
Plug thickness	0.8 mm

Connection data

Wire cross-section, min.	1.5 mm ²
Wire cross-section, max.	2.5 mm ²
Wire cross-section AWG, min.	16
Wire cross-section AWG, max.	14

Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PVC insulation
Working temperature, min.	-10 °C
Working temperature, max.	75 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

2559.0 FST 2,5/6,3



Media

Data sheet

2559.0 FST 2,5/6,3



Accessories
