

3084.0 H 2,5/17,5 KS BU

Wire-end ferrules, Max. wire cross-section: 2.5 mm², Length: 17.5 mm, Length of copper pipe: 8 mm, Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	3084.0
Article name	H 2,5/17,5 KS BU
GTIN (EAN)	4044211057893
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.2 g
Weight per piece (including packaging)	0.21 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Blue

Technical data

Dimensions

Length	17.5 mm
Length of copper pipe	8 mm
Diameter of copper pipe	2.3 mm
Diameter plastic collar	7.3 mm
Wall thickness of copper pipe	0.15 mm
Wall thickness of plastic collar	0.3 mm

Connection data

Wire cross-section, max.	2.5 mm ²
Wire cross-section AWG, max.	14
Stripping length	8 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

3084.0 H 2,5/17,5 KS BU



Approvals

Standards and regulations

DIN 46228-4:1990	yes
------------------	-----

Data sheet

3084.0 H 2,5/17,5 KS BU



Media

Accessories
