



Crimp lug, Length: 21.2 mm, Max. wire cross-section: 1.5 mm<sup>2</sup>, Colour: Red

### Business data

Article number	2555.0
Article name	FSH A 1
GTIN (EAN)	4044211053482
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	1.46 g
Weight per piece (including packaging)	1.5 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Red

### Technical data

#### Dimensions

Length	21.2 mm
Length of connector	7.8 mm
Plug width	6.3 mm
Diameter of feed-in funnel	3.5 mm
Plug thickness	0.8 mm

#### Connection data

Wire cross-section, min.	0.5 mm <sup>2</sup>
Wire cross-section, max.	1.5 mm <sup>2</sup>
Wire cross-section AWG, min.	20
Wire cross-section AWG, max.	16

#### Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PVC insulation
Working temperature, min.	-10 °C
Working temperature, max.	75 °C

#### Further technical data

Insulation available	✓
----------------------	---

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

---

**Media**

---

---

**Accessories**

---