

# Data sheet

## 3067.0 QKS G 2,5



Crimp lug, Fork shape acc. to DIN 46237/C, Max. wire cross-section: 2.5 mm<sup>2</sup>, Colour: Blue

**RAL:** Ähnlich 5005

### Business data

Article number	<u>3067.0</u>
Article name	QKS G 2,5
GTIN (EAN)	4044211057725
Connector shape	Fork shape acc. to DIN 46237/C
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.75 g
Weight per piece (including packaging)	0.77 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Blue

### Technical data

#### Dimensions

Length (input to end of inner fork ring)	18 mm
Outer width of fork	8 mm
Inner width of fork	4.3 mm
Diameter of feed-in funnel	4.5 mm
Size DIN	C 4 - 2,5

#### Connection data

Wire cross-section, min.	1.5 mm <sup>2</sup>
Wire cross-section, max.	2.5 mm <sup>2</sup>
Wire cross-section AWG, min.	16
Wire cross-section AWG, max.	14

#### Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

#### Further technical data

Insulation available	✓
Soldered	✓

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

## 3067.0 QKS G 2,5



---

### Approvals

---

#### Standards and regulations

---

Standards / specifications

DIN EN 13599

---

# Data sheet

## 3067.0 QKS G 2,5



---

### Media

---

# Data sheet

## 3067.0 QKS G 2,5



---

### Accessories

---