

3089.0 H 16,0/25,5 KS BU

Wire-end ferrules, Max. wire cross-section: 16 mm², Length: 25.5 mm, Length of copper pipe: 12 mm, Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	3089.0
Article name	H 16,0/25,5 KS BU
GTIN (EAN)	4044211057947
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.96 g
Weight per piece (including packaging)	1 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Blue

Technical data

Dimensions

Length	25.5 mm
Length of copper pipe	12 mm
Diameter of copper pipe	6 mm
Diameter plastic collar	11.9 mm
Wall thickness of copper pipe	0.2 mm
Wall thickness of plastic collar	0.3 mm

Connection data

Wire cross-section, max.	16 mm ²
Wire cross-section AWG, max.	6
Stripping length	12 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
----------------------	---

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

3089.0 H 16,0/25,5 KS BU



Approvals

Standards and regulations

DIN 46228-4:1990

yes

Data sheet

3089.0 H 16,0/25,5 KS BU



Media

Accessories
