
T	HIS COPY IS PROVIDED ON A	A RESTRICTED BASIS AND IS NOT TO BE U	SED IN	I ANY W	AY DET	RIME	NTAL TO	THE	INTERI	ESTS OF	PANDUIT CO	ORP.
	Material	High Conductivity Seamless Copper Tube										
	Plating	Electro-Tin										
	Wire Size	2000 kcmil	_	1							— .705 R I >	REF
	Wire Type	Stranded Copper; Class B: Compressed or Concentric				C(U)us	2000 kcmil STR CU LCC2000-12W	_				
	Wire Strip Length	3-5/8 in.	3.10)±.10	ANDUIL	\rightarrow	2000-		$\frac{1}{2}$			
	Stud Size	1/2 in.			'A		00 k	ĺ				
	UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.	.63±.07 —	.07 —	-		2 - 1.75±.02	2			560±.02 (2) PLS	DIA
	UL Temperature Rating	90° C			-		3.08 RE	F				
	C.S.A Certified Wire Connector	N/A			•					— 7.88±	.10 ———	
	Panduit Color Code on Barrel	Brown									-	
	Panduit Die Index No. on Barrel	N/A	Wire Inspection Window———							 		
	Alternate Industry Die Index No. () on Barrel	(34)										





						CORP. TINLEY PARK, ILLINOIS
						LCC2000-12W-1
00	4/19	JHNU	TMR	DRAWING RELEASED	046154	Copper Lug - Two-Hole, Long Barrel with Window
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCC2000-12W-CUST