



Wire-end ferrules, Max. wire cross-section: 0.75 mm², Length: 24 mm, Length of copper pipe: 18 mm, Colour: White

RAL: 9010

Business data

| | |
|--|---------------|
| Article number | 3008.0 |
| Article name | HZL 0,75 L WH |
| GTIN (EAN) | 4044211057275 |
| Packaging unit | 500 |
| Quantity unit | PC |
| Weight per piece (not including packaging) | 0.21 g |
| Weight per piece (including packaging) | 0.22 g |
| Unit of weight | G |
| Customs number | 85369010 |
| Country of origin | DE |
| Product description | Ferrules |
| Colour | White |

Technical data

Dimensions

| | |
|----------------------------------|---------|
| Length | 24 mm |
| Length of copper pipe | 18 mm |
| Width of plastic collar | 3 mm |
| Height of plastic collar | 5.5 mm |
| Diameter of copper pipe | 1.7 mm |
| Wall thickness of copper pipe | 0.15 mm |
| Wall thickness of plastic collar | 0.3 mm |

Connection data

| | |
|------------------------------|----------------------|
| Wire cross-section, max. | 0.75 mm ² |
| Wire cross-section AWG, max. | 18 |
| Stripping length | 21 mm |
| 2-wire plastic collar | ✓ |

Materials

| | |
|---------------------------|--------------------------------|
| Copper pipe | Copper alloy |
| Surface | Galvanically tin-plated, shiny |
| Plastic collar | Polypropylene homopolymer |
| Working temperature, min. | -5 °C |
| Working temperature, max. | 105 °C |

Further technical data

| | |
|----------------------|---|
| Insulation available | ✓ |
|----------------------|---|

Environmental Product Compliance

| | |
|--------------------------------|------------|
| REACH Conform | yes |
| REACH Reference date | 2023-06-14 |
| REACH Candidate Substance Note | No |
| RoHS Conform | yes |

Approvals

Standards and regulations

DIN 46228-4:1990

yes

Data sheet

3008.0 HZL 0,75 L WH



Media

Accessories
