



Crimp lug, Fork shape acc. to DIN 46237/C, Max. wire cross-section: 6 mm², Colour: Yellow

RAL: 1026

Business data

Article number	<u>3073.0</u>
Article name	QKS G 6
GTIN (EAN)	4044211057787
Connector shape	Fork shape acc. to DIN 46237/C
Product-compliant (according to DIN)	yes
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	2.71 g
Weight per piece (including packaging)	2.72 g
Unit of weight	G
Customs number	85369010
Country of origin	TW
Product description	Crimp
Colour	Yellow

Technical data

Dimensions

Length (input to end of inner fork ring)	26 mm
Outer width of fork	14 mm
Inner width of fork	8.4 mm
Diameter of feed-in funnel	26 mm
Size DIN	C 8 - 6

Connection data

Wire cross-section, min.	4 mm ²
Wire cross-section, max.	6 mm ²
Wire cross-section AWG, min.	12
Wire cross-section AWG, max.	10

Materials

Connector material	Copper
Surface	Tin-plated
insul.	Expanded PA insulation
Working temperature, min.	-55 °C
Working temperature, max.	105 °C

Further technical data

Insulation available	✓
Soldered	✓

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet

3073.0 QKS G 6



Approvals

Standards and regulations

Standards / specifications

DIN EN 13599

Media

Accessories
