

Dual Channel Differential DSL Line Driver

The EL1528 is a dual channel differential amplifier designed for driving full rate ADSL signals at very low power dissipation. The high drive capability of 450mA makes this driver ideal for both CAP and DMT designs. It contains two pairs of wideband, high-voltage, current mode feedback amplifiers optimized for low power consumption in DSL systems.

These drivers achieve an MTPR distortion measurement of better than 70dB, while consuming typically 5mA per DSL channel of total supply current. This supply current can be set using a resistor on the I_{ADJ} pin. Two other pins (C₀ & C₁) can also be used to adjust supply current to one of four pre-set modes (full-I_S, 3/4-I_S, 1/2-I_S, and full power-down). The EL1528 operates on ±5V to ±12V supplies and retains its bandwidth and linearity over the complete supply range.

The device is supplied in a thermally-enhanced 20-pin HTSSOP and the small footprint (4x5mm) 24-pin QFN packages. The EL1528 is specified for operation over the full -40°C to +85°C temperature range.

Get FULL DATASHEET

Features

- Pb-free available
- 450mA output drive capability
- 44.4V_{P-P} differential output drive into 100Ω
- -75dBc THD @ 500kHz 16V_{P-P}
- MTPR of -70dB
- Operates down to 2mA per amplifier supply current
- Current control pins
- Channel separation
 - 80dB @ 500kHz
 - 75dB @ 1MHz

Applications

- Dual port ADSL line drivers
- HDSL line drivers
- VDSL line driver

Ordering Information

PART NUMBER	PACKAGE	TAPE & REEL	PKG. DWG. #
EL1528CL	24-Pin QFN	-	MDP0046
EL1528CL-T7	24-Pin QFN	7"	MDP0046
EL1528CL-T13	24-Pin QFN	13"	MDP0046
EL1528CLZ (See Note)	24-Pin QFN (Pb-free)	-	MDP0046
EL1528CLZ-T7 (See Note)	24-Pin QFN (Pb-free)	7"	MDP0046
EL1528CLZ-T13 (See Note)	24-Pin QFN (Pb-free)	13"	MDP0046
EL1528CRE	20-Pin HTSSOP	-	MDP0048
EL1528CRE-T7	20-Pin HTSSOP	7"	MDP0048
EL1528CRE-T13	20-Pin HTSSOP	13"	MDP0048
EL1528CREZ (See Note)	20-Pin HTSSOP (Pb-free)	-	MDP0048
EL1528CREZ-T7 (See Note)	20-Pin HTSSOP (Pb-free)	7"	MDP0048
EL1528CREZ-T13 (See Note)	20-Pin HTSSOP (Pb-free)	13"	MDP0048

NOTE: Intersil Pb-free products employ special Pb-free material sets; molding compounds/die attach materials and 100% matte tin plate termination finish, which is compatible with both SnPb and Pb-free soldering operations. Intersil Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020C.

All Intersil U.S. products are manufactured, assembled and tested utilizing ISO9000 quality systems.
Intersil Corporation's quality certifications can be viewed at www.intersil.com/design/quality

Intersil products are sold by description only. Intersil Corporation reserves the right to make changes in circuit design, software and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com