



鋁 電 解 電 容 器
ALUMINIUM ELECTROLYTIC CAPACITORS

承 認 書

SPECIFICATION FOR APPROVAL

客 戶	
CUSTOMER:	<u>立创商城</u>
型 號	
SERIES:	<u>TRM SERIES</u>
規 格	
SPECIFICATION:	<u>220 μF400V/Φ 30*30</u>
日 期	
DATE:	<u>2021 年 02 月 26 日</u>

客 戶 承 認 欄 APPROVAL COLUMN			

承 制 SUPPLIER		

□伯鸿电子公司

地址：广东省佛山市南海桂城季华东路
万科金域蓝湾红霞苑 2 座 1502
TEL: 757-86368545 FAX: 757-86233516
BOR HURNG ELECTRONIC CO., LTD.

ADD: Guangdong Province, Foshan City
Nanhai Guicheng Jihua road Vanke
Golden Mile Island 2 1502 yuan
Hongxia
TEL: 757-86368545 FAX: 757-86233516

□伯鸿电子公司

地址：广东省东莞市长安长盛西路莲花
苑 D 区芙蓉阁 A 座 401
TEL: 769-85312879 FAX: 769-85416647
BOR HURNG ELECTRONIC CO., LTD.

ADD: Dongguan City, Changan Province,
Guangdong Chang Sheng Road, lotus
garden D District lotus Pavilion A
block 401
TEL: 769-85312879 FAX: 769-85416647

□伯鸿电子(肇庆)有限公司

地址：广东省肇庆市端州一路沙湖工业区。
TEL: 758-2710158 FAX: 758-2734058
**BOR HURNG ELECTRONIC (ZHAOQING)
CO., LTD.**

ADD: SHAHU INDUSTRIAL ZONE DUANZHOU 1
RD., ZHAOQING CITY GUANGDONG PR-
OVINCE.
TEL: 758-2710158 FAX: 758-2734058



承 认 内 容
FOR APPROVAL

客 户

CUSTOMER: 立创商城

料号 P/N: CK221M0I30B	系列 Electrolytic Capacitors Series TRM	规格 Specif. 220uF400V/ φ 30*30
-------------------------------	---	---


电性能 Electric characteristics

工作电压 W. V. (V-DC)	标称容量 Nom. Cap. (uF)	容量允差 Cap. Tol. (%) At 120Hz/25°C	外形尺寸 Case Size D×L (mm)	漏电流 L. C. (uA) 5minutes/25°C	损失角 D. F. At 120Hz/25°C
400	220	±20%	30*30	890	0.20
ESR 值 E. S. R. (Ω) At 100kHz/25°C	浪涌电压 S. V. (V-DC)	使用温度 Oper. Temp. (°C)	纹波电流 Rip. Cur (A) At 120Hz/85°C	高温负荷 Load Life (HRS/85°C)	高温贮存 Shelf Life (HRS/85°C)
-----	450	-25~+85	1.05	2000	500

高温负荷特性 Load Life	在 85°C 环境中对电容器施加额定工作电压连续 2000 小时, 经恢复后于常温 25°C 测试, 其性能符合下表要求 After applying rated working voltage for 2000 hours at 85°C and then being stabilized at +25°C, capacitors shall meet following limits				
	静电容量变化率 Capacitance change	初测值的 ±20% 以内 Within ±20% of the initial measured value			
	损失角正切值 Dissipation Factor	不大于规定值的 200% Less than 200% of the specified value			
	漏电流 Leakage Current	不大于规定值 Within specified value			

高温贮存特性 Shelf Life	在 85°C 环境中 (不加电压) 放置 500 小时, 经恢复后于常温 25°C 测试, 其性能符合下表要求 After storage for 500 hours at 85°C With no voltage applied and then being stabilized at +25°C, capacitors shall meet following limits				
	静电容量变化率 Capacitance change	初测值的 ±20% 以内 Within ±20% of the initial measured value			
	损失角正切值 Dissipation Factor	不大于规定值的 200% Less than 200% of the specified value			
	漏电流 Leakage Current	不大于规定值的 200% Less than 200% of the specified value			

尺寸 Diagram: (Unit:mm)



本体尺寸 Case Size	
外径 D	长度 L
30	30

作成 Designet	罗家玲	审核 Auditor		核准 Approved	
----------------	-----	---------------	--	----------------	--

客户承认 CUSTOMER SIGNATURE					
-------------------------------	--	--	--	--	--