
	12	11		10	9	8	7			
	LOOSE	E PIECE	SPECIFICATIONS							
Н	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.			
	191700007	B-119-06	6	.146 [3.71]						
	191700009	B-119-08	8	.173 [4.39]	.350 [8.89]	.271 [6.88]	.752 [19.10]			
	191700011	B-119-10	10	.198 [5.03]						
G										



6

5

4

3

2

1

## NOTES:

1. MATERIAL:

TERMINAL: COPPER ( STOCK TKN .031±.001 [0.79] )

PLATING: ELECTRO-TIN (.0003 MIN).

2. WIRE SIZE: 16 -14 AWG

1.0 - 2.5 MM<sup>2</sup>

3. "UL" LISTING #E32244

"CSA" LISTING #18689

4. ALL DIMENSIONS IN INCHES/[MM].

5. PARTS ARE ROHS COMPLIANT.

6. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS P1 RELEASE DATE 2019/10/18 22:51:26

10

SYMBO	OI S	THIS DRAWING	G CONTA	AINS INF	ORMATION THA	T IS PROPRIET	ARY TO MOLEX E	LECTRONIC TECH	HNOLO	GIES, LLC AND SHO	OULD NOT BE U	SED WIT	HOUT WR	ITTEN PER	RMISSION	
	OLO	DIMENSION UNITS SCALE			CURREN	CURRENT REV DESC:										
= 0		INCH/MM	N	ITS						molex						
<u></u>	0		GENERAL TOLERANCES (UNLESS SPECIFIED)													
=	0	, L	MM	INC	EC NO:	625848			HOOK TONGUE TERM					1INAL		
\ <u>\</u> \\\ =	0	4 PLACES ±		±	- DRWN:	ABENJA	MINLW	2019/09/13		KRIMPTITE 100-SERIES						
vannanna V	_	3 PLACES ±		± .00	5 CHK'D:	GROJAS	S01	2019/10/17								
=	0	2 PLACES ±	0.13	± .0	1 APPR:	JMACNE	EIL	2019/10/18		PRODUCT CUSTOMER DRAWING						
<u>c</u> =	0	1 PLACE ±	0.25	±	- INITIAL	REVISIO	N:	Ī		DOCUMENT NUMBER DOC				PE DOC PART REVISION		
<b>X</b> =	0	0 PLACES ±		±	DRWN:	KO		1984/10/15		BCD1	0102		PSD	001		
	_	ANGULAR	R TOL	± 0.5	APPR:					ВСВТ	0102		1500	001	A	
=	0	DRAFT WH	IERE APPL	ICABLE	THIRD ANGL	E PROJECTION	DRAWING	SERIES	MATE	RIAL NUMBER	CUSTOMER		•	SHEET	NUMBER	
© =	0	0 MUST REMAIN WITHIN DIMENSIONS					C-SIZE	19170	5	SEE TABLE GENERAL MARKET		RKET	1 OF 1			
		5			4		3	2			1					