

Type_No	Description	CECC	Polarity	Package	Ic_cont	Hfe_at	Vce_ic	fT	Pd	Vceo
1N 914CSM	Ceramic Surface Mount		diode	LCC1	150mA					100
1N4001CSM	Ceramic Surface Mount		diode	LCC1	1					100
1N4001QCSM	Quad diode in LCC2		diode	LCC2						100
1N4003CSM4	Ceramic Surface Mount		diode	LCC3	1.0					200
1N4003QCSM	4x hermetic		diode	LCC2	1.0					200
1N4148CSM	Ceramic Surface Mount		diode	LCC1	150mA					75
1N4151CSM	Ceramic Surface Mount		diode	LCC1	150mA					75
1N4572ACSM D	hermetic SM		zener	LCC2						6.4v
1N5617CSMD	hermetic SM		diode	LCC2	1.0					400
1N5711CSM	Ceramic Surface Mount		diode	LCC1	15mA					70
2C 415			NPN	TO77	0.03	100min	5/0.1m	100M	1.1	35
2C 425			NPN	TO77	0.1	35min	10/0.05	40M	1.5	75
2C 444			NPN	TO77	0.05	40min	5/10m	200M	1.3	35
2C 746			NPN	TO77	0.1	35min	5/50m	200M	1.8	50
2N1132			PNP	TO39	0.6	30-90	10/0.15	50M	0.6	50
2N1208			NPN	TO61	5	15min	12/2	3M	85	60
2N1209			NPN	TO61	5	20min	12/2	3M	85	45
2N1483A			NPN	TO8	3	20-200	4/0.75	1.2M	25	40
2N1484A			NPN	TO8	3	20-200	4/0.75	1.2M	25	55
2N1485A			NPN	TO8	3	35-200	4/0.75	1.2M	25	40
2N1486A			NPN	TO8	3	35-200	4/0.75	1.2M	25	55
2N1507			NPN	TO39	1	150t	10/0.15	50M	0.6	30
2N1613			NPN	TO39	0.5	40-120	10/0.15	70M	0.8	50
2N1613L			NPN	TO5	0.5	40-120	10/0.15	70M	0.8	50
2N1616			NPN	TO61	5	15-75	12/2	3M	85	60
2N1617			NPN	TO61	5	15-75	12/2	3M	85	70
2N1618			NPN	TO61	5	15-75	12/2	3M	85	80
2N1711			NPN	TO39	0.5	40-120	10/0.15	70M	0.8	50
2N1716			NPN	TO39	0.75	40min	5/0.2	16M	0.8	60
2N1721				TO5Slug						
2N1724			NPN	TO61	5	20-90	15/2	10M	100	80
2N1724A			NPN	TO61	5	30-90	15/2	10M	100	12
2N1725			NPN	TO61	5	50-150	15/2	10M	100	80
2N1889			NPN	TO39	0.25	40-120	10/0.15	50M	0.8	60
2N1890			NPN	TO39	0.25	100-300	10/0.15	50M	0.8	60
2N1893			NPN	TO39	0.5	30min	5/1m	50M	0.8	80
2N1936			NPN	TO63	20	10-50	10/10	4M	150	60
2N1937			NPN	TO63	20	10-50	10/10	4M	150	80
2N1991			PNP	TO39	0.3	15-60	10/0.15	40M	0.6	20
2N2060			PNP	TO77	0.5	40-120	5/10m	60M	0.6	80
2N2060A			PNP	TO77	0.5	40-120	5/10m	60M	0.6	80
2N2060DCSM	Dual device in CSM		PNP	LCC2	0.5	40-120	5/10m	60M	0.6	80
2N2102			NPN	TO39	1	35min	10/10m	60M	1	65
2N2192			NPN	TO39	1	100-300	10/0.15	50M	0.8	40
2N2192A			NPN	TO39	1	100-300	10/0.15	50M	0.8	40
2N2192L			NPN	TO5	1	100-300	10/0.15	50M	0.8	40
2N2193			NPN	TO39	1	40-120	10/0.15	50M	0.8	50
2N2193A			NPN	TO39	1	40-120	10/0.15	50M	0.8	50
2N2194			NPN	TO39	1.0	2.5		50M	800mW	40
2N2194A			NPN	TO39	1.0	2.5		50M	800mW	40
2N2218			NPN	TO39	0.8	40-120	10/0.15	250M	0.8	30
2N2218 CECC		50002-100	NPN	TO39	0.8	40-120	10/0.15	250M	0.8	40
2N2218A			NPN	TO39	0.8	40-120	10/0.15	250M	0.8	40
2N2218A CECC		50002-100	NPN	TO39	0.8	40-120	10/0.15	250M	0.8	40
2N2218AQF	Quad Ceramic Flat Pack		NPN	Ceramic Flat	0.8	40-120	10/0.15	250M	2.0	40
2N2219			NPN	TO39	0.8	100-300	10/0.15	250M	0.8	30
2N2219 CECC		50002-100	NPN	TO39	0.8	100-300	10/0.15	250M	0.8	40
2N2219A			NPN	TO39	0.8	100-300	10/0.15	250M	0.8	40
2N2219A CECC		50002-100	NPN	TO39	0.8	100-300	10/0.15	250M	0.8	40
2N2219AL			NPN	TO5	0.8	100-300	10/0.15	250M	0.8	40
2N2219AQF	Quad Ceramic Flat Pack		NPN	Ceramic Flat	0.8	100-300	10/0.15	250M	2.0	40
2N2221			NPN	TO18	0.8	40-120	10/0.15	250M	0.5	30
2N2221 CECC		50002-101	NPN	TO18	0.8	40-120	10/0.15	250M	0.5	40
2N2221A			NPN	TO18	0.8	40-120	10/0.15	250M	0.5	40
2N2221A CECC		50002-101	NPN	TO18	0.8	40-120	10/0.15	250M	0.5	40
2N2221ACSM	Ceramic Surface Mount		NPN	LCC1	0.8	40-120	10/0.15	250M	0.5	40
2N2221ACSM CECC	Ceramic Surface Mount	50003-059	NPN	LCC1	0.8	40-120	10/0.15	250M	0.5	40
2N2221ADCSM	Dual device in CSM		NPN	LCC2	0.8	40-120	10/0.15	250M	0.6	40
2N2221ADCSM	Dual device in CSM	50003-059	NPN	LCC2	0.8	40-120	10/0.15	250M	0.6	40
2N2221AQF	Quad Ceramic Flat Pack		NPN	Ceramic Flat	0.8	40-120	10/0.15	250M	2.0	40
2N2221CSM			NPN	LCC1	0.8	40-120	10/0.15	250M	0.5	30
2N2221CSM CECC			NPN	LCC1	0.8	40-120	10/0.15	250M	0.5	30
2N2221DCSM	Dual device in CSM		NPN	LCC2	0.8	40-120	10/0.15	250M	0.6	40
2N2221DCSM	Dual device in CSM	50003-059	NPN	LCC2	0.8	40-120	10/0.15	250M	0.6	40
2N2222			NPN	TO18	0.8	100-300	10/0.15	250M	0.5	30
2N2222 CECC		50002-101	NPN	TO18	0.8	100-300	10/0.15	250M	0.5	40
2N2222A			NPN	TO18	0.8	100-300	10/0.15	250M	0.5	40
2N2222A CECC		50002-101	NPN	TO18	0.8	100-300	10/0.15	250M	0.5	40
2N2222ACSM	Ceramic Surface Mount		NPN	LCC1	0.8	100-300	10/0.15	250M	0.5	40
2N2222ACSM CECC	Ceramic Surface Mount	50003-059	NPN	LCC1	0.8	100-300	10/0.15	250M	0.5	40
2N2222ACSM4	Ceramic Surface Mount		NPN	LCC3	0.8	100-300	10/0.15	250M	0.5	40
2N2222ADCSM	Dual device in CSM		NPN	LCC2	0.8	100-300	10/0.15	250M	0.6	40