


PVC INSULATED FLANGE SPADE TERMINALS



Specifications

- **Maximum Electrical Rating:** 600 Volts
- **Maximum Temperature:** +105°C
- **Terminal Material:** Copper
- **Plating:** Electro Tin Plated
- **Insulation Material:** Vinyl (PVC)



Ordering Information:

Wire Range AWG / mm ²	NTE Part Number	Stud Size d2	Dimensions inch(mm)						
			B	L	F	E	D	d1	W
22 - 18 AWG 0.5 - 1.5mm ²	76-IFST22-06	#6 (3.7)	.252 (6.4)	.748 (19.0)	.248 (6.3)	.394 (10.0)	.161 (4.1)	.067 (1.7)	.059 (1.5)
	76-IFST22-08	#8 (4.3)	.283 (7.2)	.768 (19.5)	.248 (6.3)	.394 (10.0)	.161 (4.1)	.067 (1.7)	.059 (1.5)
	76-IFST22-10	#10 (5.3)	.315 (8.0)	.768 (19.5)	.276 (7.0)	.394 (10.0)	.161 (4.1)	.067 (1.7)	.059 (1.5)
16 - 14 AWG 1.5-2.5mm ²	76-IFST16-06	#6 (3.7)	.252 (6.4)	.768 (19.5)	.248 (6.3)	.394 (10.0)	.177 (4.5)	.091 (2.3)	.059 (1.5)
	76-IFST16-08	#8 (4.3)	.283 (7.2)	.776 (19.7)	.256 (6.5)	.394 (10.0)	.177 (4.5)	.091 (2.3)	.059 (1.5)
	76-IFST16-10	#10 (5.3)	.335 (8.5)	.807 (20.5)	.287 (7.3)	.394 (10.0)	.177 (4.5)	.091 (2.3)	.059 (1.5)
12 - 10 AWG 4-6mm ²	76-IFST12-06	#6 (3.7)	.283 (7.2)	.945 (24.0)	.295 (7.5)	.492 (12.5)	.256 (6.5)	.134 (3.4)	.059 (1.5)
	76-IFST12-08	#8 (4.3)	.335 (8.5)	.945 (24.0)	.295 (7.5)	.492 (12.5)	.256 (6.5)	.134 (3.4)	.059 (1.5)
	76-IFST12-10	#10 (5.3)	.374 (9.5)	.945 (24.0)	.295 (7.5)	.492 (12.5)	.256 (6.5)	.134 (3.4)	.059 (1.5)
	76-IFST12-1/4	1/4 (6.5)	.374 (9.5)	.945 (24.0)	.295 (7.5)	.492 (12.5)	.256 (6.5)	.134 (3.4)	.059 (1.5)