

Product: DB59BNCSL-25 ☑



Double Bubble RG-59 BNC Coax Compression Connector

Product Description

Double Bubble RG59 BNC connector, fits most CCTV Security coaxial cables. Compression design that molds the metal completely around the cable. 25 per Pack

Technical Specifications

Product Overview Suitable Applications: Security CCTV **Physical Characteristics (Overall)** Packaging: 25 Pack Number of Pieces: 1 Connectors Materials Material Nickel plated Brass Gold Plated **Electrical Characteristics** Impedance Nominal Characteristic Impedance 75 Ohm Return Loss (RL) Frequency [MHz] DC-1 GHz 27 dB Return Loss 1.07 VSWR DC-2 GHz 27 dB Return Loss 1.09 VSWR DC-3 GHz 29 dB Return Loss 1.09 VSWR Electrical Characteristics Notes: Cable Pullout Force Exceeding 65 in/lbs. **Mechanical Characteristics**

Footprint/Type:	Соах	
Connector Interface Type:	BNC	
Gender:	Male - plug	
Connector Series Name:	Double Bubble	
Locking:	No	
Tool Compatibility:	CPLCRBC-BR (compression), PSA59/6 (strip)	
Termination Type:	Compression	
Cable Center Conductor Diameter Limits:	.03170339 inch	
Cable Dielectric Diameter Limits:	.137148 inch	
Cable Outer Jacket Diameter Limits:	.232248 inch	

Standards

RG Type:	59
Series Type:	59

Applicable Environmental and Other Programs

EU CE Mark:	Yes
Suitability	
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Related Part Numbers

Variants		
	Color	UPC
DB59BNCSL-25 N		
	0 00101	
Patent:		
listory		
Update and Revisior		

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or guality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.