

3196.2 STD-TS/LED(GN) GR



Switchgear cabinet socket with LED, Mounting type: TS 35/7.5, Width: 45 mm, Colour: Grey

RAL: 7032

Business data

Article number	<u>3196.2</u>
Article name	STD-TS/LED(GN) GR
GTIN (EAN)	4044211141844
Packaging unit	5
Quantity unit	PC
Weight per piece (not including packaging)	69 g
Weight per piece (including packaging)	77.6 g
Unit of weight	G
Customs number	85369010
Country of origin	CN
Product description	Switchgear cabinet socket with LED
Colour	Grey

3196.2 STD-TS/LED(GN) GR

Technical data

Dimensions

Length	75 mm
Width	45 mm
Height TS 35/7.5	67 mm

Ratings

Rated voltage	250 AC V
Rated current	16 AC A

Connection data

Wire cross-section single-core (rigid) / stranded, min.	0.2 mm ²
Wire cross-section single core (rigid)/stranded, max.	4 mm ²
Wire cross-section stranded, min.	0.2 mm ²
Wire cross-section stranded, max.	2.5 mm ²
Wire cross-section stranded with wire-end ferrules,min.	0.2 mm ²
Wire cross-section stranded with wire-end ferrules,max.	2.5 mm ²
Wire cross-section AWG, min.	24
Wire cross-section AWG, max.	12
Stripping length	8 mm
Screw threading	M 3
Tightening torque, min.	0.5 Nm
Tightening torque, max.	1 Nm

Materials

Insulation housing	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-20 °C
Working temperature, max.	60 °C
Material locking foot	Metal

Further technical data

Illuminated display	LED, green with series resistor
---------------------	---------------------------------

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

Standards and regulations

Standards / specifications

Directive 2014/35/EU, DIN 49440-1:2006-01, DIN
VDE 0620-1:2016-01

Media

3196.2 STD-TS/LED(GN) GR

Accessories

Markers



Device and installation markers / Maxicard, Length: 17 mm, Width: 8 mm, Colour: White

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3321.7</u>	MC GS 8/17 R t WH	4044211119058	200 ST
