12	11 1	0 9	8	7	6	5	4	ORDER NO	3	2 WOODHEAD NO.	1 COLOR
								130147-0104		29W74MB	YELLOW
								130147-0104	-		
		3									
			Ø (2.75) [(69.8)]								
		FACE VIEW	(1.12)— 〔(28.3〕		- (2.00) [(50.8)]	► - (2.54 〔(64.6	_				
ITEM NO.	DESCRIPTIONS	MATERIAL	QT	Y.							·
1	BLADE	BRASS, NICKEL PLATED	4								
2	RETAINING SCREWS	STAINLESS STEEL	2				л	NOTE:			
3	CLAMP AND TERMINAL SCREW ASSY	BRASS, ZINC PLATED	4						T CABLE	E RANGE FROM .	562" TO 1.00""
4	INSERT	NYLON	1		SYMB	OLS THIS DRAWING CONTAINS IN DIMENSION UNITS SCALE	FORMATION THAT IS PRO	PRIETARY TO MOLEX EL		INOLOGIES, LLC AND SHOULD NOT BE U	SED WITHOUT WRITTEN PERMISSION
5	TERMINAL COVER	POLYCARBONATE	1		¥ =	O INCH[MM] NTS		DESC:		mo	
6	HOUSING	SILICONE WITH NYLON THREAD	1		\F_ = \F_ =	0 GENERAL TOLERANCES (UNLESS SPECIFIED))	35			
7	GROMMET	RUBBER	4		¥ =	0 4 PLACES ± ±	CH EC NO: 6176 DRWN: SRP	ATIL	2019/02/18	WATERTITE CONNEC 3P4W I	
8	FRICTION RING	NYLON	1		=		CHK'D: DNG	IEELAND	2019/05/21 2019/10/16	PRODUCT CUST	OMER DRAWING
9	COMPRESSION NUT	NYLON	1		= \\	0 1 PLACE ± ± 0 0 PLACES ± ±	INITIAL REV DRWN: SRP		2019/02/18	DOCUMENT NUMBER	DOC TYPE DOC PART REVISION
10	CABLE GLOVE	SILICONE	1		■ =	0 ANGULAR TOL ± 0 DRAFT WHERE APPLICABLE	• APPR: HKN THIRD ANGLE PROJEC	IEELAND	2019/10/16		PSD 000 A
FORMAT: Eng-lega-master-to-prod-C REVISION D DATE: 2019/01/8	STATUS P1 RELEASE DATE 2019/10/1	6 04:10:47 0 9	8		6	MUST REMAIN		C-SIZE	130147 3	SEE TABLE GENER	AL MARKET 1 OF 1





