


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.





10.3

| REVISION | | | | | | | |
|----------|-------------|------|----------|--|--|--|--|
| REV. | DESCRIPTION | DATE | APPROVED | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |




NOTES:

TOP COVER COLOR: WHITE BODY INSULATOR COLOR: WHITE RATING: 10A 250V AC APPROVALS: SAA PANEL THICKNESS: 3.5mm **RoHS COMPLIANT**

CONTROLLED

| 3 | Screw | Screw N0.6-18 Nickel Plated | | | | | |
|----|--------------------------------|-----------------------------|-------------------------------------------|-----------------|-------------------|--|--|
| 2 | 2 Screw M4*0.7mm Nickel Plated | | | | | | |
| 1 | Brass t | Brass t=0.5mm | | | | | |
| | Dim ange | Tolerance +/- | Qualtek Electronics Corp. PPC DIVISION | | | | |
| | (mm) | (mm) | Part Number: | 741W-E/01 | RoHS Compliant | | |
| | 0-1 | 0.15 | Description: AUSTRALIA AC RECEPTACLE | | | | |
| | 1-6 | 0.20 | | USTRALIA AC REC | EPIACLE | | |
| | 6-18 | 0.30 | | | | | |
| 1 | 18-50 | 0.50 | | UNIT: mm | | | |
| 5 | 50-120 | 0.70 | Drawn / Date | Checked / Date | Approved / Date | | |
| 12 | 20-250 | 0.90 | R.Nuti | | | | |
| 25 | 50-500 | 1.20 | 10-07-19 | 10-07-19 | | | |



PANEL CUTOUT