## SIEMENS

## Data sheet

## 6ES7972-0BA61-0XA0

## product type designation

product description



PROFIBUS plug, 35°

PROFIBUS bus connector, RS 485, Fast Connect, without programming port,  $35^{\circ}$ 

SIMATIC DP, Connection plug for PROFIBUS up to 12 Mbit/s 35 degree cable outlet, Insulation displacement method FastConnect, without PG socket 15.8x 54x 39.5 mm (BxHxD)

suitability for use	for connecting PROFIBUS nodes to the PROFIBUS bus cable
transfer rate	
transfer rate / with PROFIBUS DP	9.6 kbit/s 12 Mbit/s
interfaces	
number of electrical connections	
for PROFIBUS cables	2
<ul> <li>for network components or terminal equipment</li> </ul>	1
type of electrical connection	
for PROFIBUS cables	Integrated insulation displacement contacts for 2-wire PB FC installation cables
<ul> <li>for network components or terminal equipment</li> </ul>	9-pin sub D connector
type of electrical connection / FastConnect	Yes
mechanical data	
design of terminating resistor	Resistor combination integrated and connectable via slide switch
material / of the enclosure	plastic
locking mechanism design	Screwed joint
design, dimensions and weights	
type of cable outlet	35 degree cable outlet
width	15.8 mm
height	54 mm
depth	39.5 mm
net weight	29 g
ambient conditions	
ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +60 °C
<ul> <li>during storage</li> </ul>	-40 +70 °C
during transport	-40 +70 °C
protection class IP	IP20
product features, product functions, product components / general	
product feature	
silicon-free	Yes
product component	
<ul> <li>PG connection socket</li> </ul>	No
strain relief	Yes
standards, specifications, approvals	
certificate of suitability	

RoHS conformity	Yes
UL approval	Yes
reference code	
<ul> <li>according to IEC 81346-2</li> </ul>	XF
further information / internet-Links	
Internet-Link	
<ul> <li>to website: Selection guide for cables and connectors</li> </ul>	https://sie.ag/2QdlxcP
last modified:	7/7/2022 🖸