SIEMENS

Data sheet

6ES7972-0BB70-0XA0

product type designation

product description



PROFIBUS plug, 90°, with PG socket

PROFIBUS bus connector, RS 485, Fast Connect, with programming port, 90°

SIMATIC DP, Connection plug for PROFIBUS up to 12 Mbit/s 90° cable outlet, 15.8x 72.2x 36.4 mm (WxHxD), Insulation displacement method FastConnect, With PG receptacle

suitability for use	for connecting PROFIBUS nodes to the PROFIBUS bus cable
transfer rate	
transfer rate / with PROFIBUS DP	9.6 kbit/s 12 Mbit/s
interfaces	
number of electrical connections	
 for PROFIBUS cables 	2
 for network components or terminal equipment 	1
type of electrical connection	
• for PROFIBUS cables	Integrated insulation displacement contacts for 2-wire PB FC installation cables
 for network components or terminal equipment 	9-pin sub D connector
type of electrical connection / FastConnect	Yes
mechanical data	
design of terminating resistor	Resistor combination integrated and connectable via slide switch
material / of the enclosure	plastic
locking mechanism design	Screwed joint
design, dimensions and weights	
type of cable outlet	90 degree cable outlet
width	15.8 mm
height	72 mm
depth	36.4 mm
net weight	45 g
ambient conditions	
ambient temperature	
 during operation 	-25 +60 °C
 during storage 	-40 +70 °C
during transport	-40 +70 °C
protection class IP	IP20
product features, product functions, product components	/ general
product feature	
• silicon-free	Yes
product component	
 PG connection socket 	Yes
strain relief	Yes
standards, specifications, approvals	
certificate of suitability	

RoHS conformity	Yes
UL approval	Yes
reference code	
 according to IEC 81346-2 	XF
further information / internet-Links	
Internet-Link	
 to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP

last modified: 7/7/2022 🖸