







2 WAYS POWER DIVIDER 0.8 - 2.2GHZ

PAGE 1/2	ISSUE 31-03-20B	SERIES SPLITTER	PART NUMBER R434512001
----------	------------------------	---------------------------	-------------------------------









All dimensions are in mm. Tolerances according ISO 2768 m-K

Weight Specification **61,0000** g







2 WAYS POWER DIVIDER 0.8 - 2.2GHZ

PAGE 2/2	ISSUE 31-03-20B	SERIES SPLITTER	PART NUMBER R434512001
-----------------	------------------------	---------------------------	-------------------------------

ELECTICAL CHARACTERISTICS

Frequency range :	0.8 – 2.2 GHz
Number of ways	2
Phase	0°
VSWR	
Input	1.3
Output	1.3
Impedance	50 Ohms
Insertion loss	0.4 dB max
Isolation	20 dB mini
Amplitude balance	± 0.3 dB
Phase Balance	± 2°
Average Power	
VSWR load < 1.2	30W
VSWR load : inf	1W

MECHANICAL CHARACTERISTICS

Connectors:	
Input	SMA female
Output	SMA female
Body	Aluminium
Finish	Blue Paint

ENVIRONMENTAL CHARACTERISTICS

Operating temperature	-40 / +85 °C
Storage temperature	-55 / +125 °C