







2 WAYS POWER DIVIDER 1 - 2GHZ

PAGE 1/2 ISSUE 21-08-17A SERIES SPLITTER PART NUMBER R434212000









All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **34,0000** g







PAGE 2/2 ISSUE 21-08-17A SERIES PART NUMBER R434212000

SPLITTER

ELECTICAL CHARACTERISTICS

Frequency range :	1 - 2 GHz
Number of ways	2
Phase	0°
VSWR	
Input	1.3
Output	1.3
Impedance	50 Ohms
Insertion loss	0.3 dB max
Isolation	23 dB mini
Amplitude balance	± 0.3 dB
Phase Balance	± 2°
Average Power	
VSWR load < 1.2	30W
VSWR load : inf	1W

MECHANICAL CHARACTERISTICS

Connectors :	
	SMA female
Output	SMA female
Body	Aluminium
Finish	Blue Paint

ENVIRONMENTAL CHARACTERISTICS

Operating temperature	-40 / +85 °C
Storage temperature	-55 / +125 °C