







4 WAYS POWER DIVIDER 5.8 - 6.4GHZ

PAGE 1/2 ISSUE 19-09-16A SERIES SPLITTER PART NUMBER R434414003









All dimensions are in mm.

Weight Specification **76,3920** g







4 WAYS POWER DIVIDER 5.8 - 6.4GHZ

PAGE 2/2	ISSUE 19-09-16A	SERIES SPLITTER	PART NUMBER R434414003
-----------------	------------------------	---------------------------	-------------------------------

ELECTICAL CHARACTERISTICS

Frequency range :	5.8 – 6.4 GHz
Number of ways	4
Phase	0°
VSWR	
Input	1.4
Output	1.4
Impedance	50 Ohms
Insertion loss	0.6 dB max
Isolation	20 dB mini
Amplitude balance	± 0.5 dB
Phase Balance	± 6°
Average Power	
VSWR load < 1.2	30W
VSWR load : inf	1W

MECHANICAL CHARACTERISTICS

Connectors :	
Input	SMA female
Output	SMA female
Body	Aluminium
Finish	Blue Paint

ENVIRONMENTAL CHARACTERISTICS

Operating temperature	-40 / +85 °C
Storage temperature	-55 / +125 °C