




4 WAYS POWER DIVIDER 1 - 3GHZ



PAGE 1/2 ISSUE 15-09-16A SERIES PART NUMBER R434514005
SPLITTER







All dimensions are in mm.

Weight Specification **111,2310** g







PAGE 2/2 ISSUE 15-09-16A SERIES SPLITTER PART NUMBER R434514005

ELECTICAL CHARACTERISTICS

Frequency range :	1 – 3 GHz
Number of ways	4
Phase	0°
VSWR	
Input	1.5
Output	1.5
Impedance	50 Ohms
Insertion loss	0.9 dB max
Isolation	18 dB mini
Amplitude balance	± 0.5 dB
Phase Balance	± 6°
Average Power	
VSWR load < 1.2	30W
VSWR load : inf	1W

MECHANICAL CHARACTERISTICS

Connectors :	
Input	SMA female
Output	SMA female
Body	Aluminium
Finish	Blue Paint

ENVIRONMENTAL CHARACTERISTICS

Operating temperature	-40 / +85 °C
Storage temperature	-55 / +125 °C